# KS 10.0 with Tcoil

**Product information** 



## **Product description**



# **Premium performance**

•
•
•
<u> </u>
IP68 <sup>1</sup>
30.5 x 12.7 x 8.0mm (1.20 x .50 x .31")
2.4 g (0.08 oz)
3 h
1.5 h
g 10 min.
111
47
<100 - >8000
114
51
<100 - >8000
122
59
<100 - 6300
132
71
<100 - 6100

Automatic	Premium	Features	Premium
Quiet	•	Directional Microphone	•
Noise	•	Speech Boost	•
Comfort	•	SNR-Boost	•
Music	•	Touch Control	•
Loud Noise	•	DuoTel	•
Car	•	HiFrequency Protect+	•
Echo	•	User Preference Tuning	•
Streamed speech	•	Real Ear Effect	•
Streamed music	•	Finetuning Channels	20
Additional programs		Dynamic Noise Manager	•
Max. additional programs	4	Feedback Manager	•
Echo	•	Noise Manager	•
Loud Noise	•	Wind Manager	•
Speech Direct	•	Echo Manager	•
Noise	•	Motion Sense	•
Quiet	•	Impulse Manager	•
Comfort	•	Binaural Sync	•
Music	•	AOV	•
Acoustic phone	•	Tinnitus	•
Custom program	•	Adaptation Control	•
Streaming programs		Balance	•
Phone call + mic	•		
PartnerMic + mic	•		

### **Housing colors**



Beige



Bronze





Stone







Remote Control

P8 Black

<sup>1</sup> IP68 indicates that the hearing aid is water and dust resistant. It survived continuous immersion in 1 meter of water for 60 minutes and 8 hours in a dust chamber as per the IEC60529 standard.

 $<sup>2\,</sup>$  Actual charging time depends on the remaining battery life, but it will not exceed 3 hours.

# **Fitting**

Phonak Target	7.1 or higher
Noahlink Wireless	•

# **Acoustic coupling**

	S Receiver	M Receiver	P Receiver	UP Receiver
Length				
Available in four different lengths (0, 1, 2, 3), left and right	•	•	•	•
Dome				
Cap dome	•	•	•	
Open dome Available in three sizes (S, M, L)	•	•	•	
Vented dome Available in three sizes (S, M, L)	•	•	•	
Power dome Available in three sizes (S, M, L)	•	•	•	
SlimTip*				
Acrylic	•	•	•	
Silicone	•	•	•	
cShell				
Acrylic	•	•	•	•
Fitting Range	dB HL  0 10 20 30 40 50 60 70 80 90 110 125 250 500 1k 2k 4k 8k  Mild to moderately- severe hearing loss.	dB HL  0 10 20 30 40 50 60 60 60 10 110 110 110 110 110 110 11	dB HL  0 10 20 30 40 40 50 60 70 80 90 100 110 125 250 500 1k 2k 4k 8k  Mild to severe hearing loss.	dB HL  0  10  20  30  40  50  60  70  80  90  110  125 250 500 1k 2k 4k  Moderate to profound hearing loss.

<sup>\*</sup>Available with extra canal length option

# KS 10.0 charging options



#### **Charger Case**

The Charger Case is a charger and protective hard case available in a robust and splash-proof housing.



#### Easy Line Power Pack

For charging KS 10.0 on the go, the Power Pack can be easily attached to the bottom of the Charger Case.

#### Bluetooth® versions

Direct calls / audio streaming	Bluetooth® 4.2 wireless technology and most older Bluetooth phones

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Sonova AG is under license.

## Wireless communication portfolio

	KS 10.0
Wireless accessory	
Easy Line TV Connector	•
Easy Line PartnerMic	•
Easy Line Remote Control	•
Apps	
Easy Line Remote™	•